

Pressure gauge OH-8-BL

Part number: 10090

FESTO



Data sheet

Feature	Value
Operating pressure	-0.1 MPa...0.8 MPa -1 bar...8 bar -14.5 psi...116 psi
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Pneumatic connection	Barbed fitting PK-3
Note on materials	RoHS-compliant