

Exhaust air flow control valve GRE-1/2

Part number: 10353

FESTO



Data sheet

Feature	Value
Valve function	Sound pressure flow control function
Selection of additional function	with muffler
Pneumatic connection 1	G1/2
Adjusting element	Slotted screw
Type of mounting	Screw-in
Standard nominal flow rate in flow control direction	3600 l/min
Standard flow rate 6->0 bar	0 l/min...4300 l/min
Operating pressure	0 bar...10 bar
Ambient temperature	-10 °C...70 °C
Mounting position	Any
Operating medium	Compressed air as per ISO 8573-1:2010 [7:::]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-10 °C...70 °C
Product weight	75 g
Material of screwed plug	Wrought aluminum alloy
Note on materials	RoHS-compliant
Seals material	NBR
Material of adjusting screw	Brass