


Axial kit
EAMM-A-R27-57A
Part number: 1133403



Data sheet

Feature	Value
Nominal length	26 mm
Mounting position	Any
Max. rotational speed	10000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	0.355 kgmm ²
Transferable torque	1.6 Nm
Product weight	170 g
Interface code, actuator	R27
Interface code, motor in	57A
Note on materials	RoHS-compliant