

Hydraulic cushioning cylinder DYHR-25-40-Y5

Part number: 1155694



Data sheet

Feature	Value
Size	25
Stroke	40 mm
Cushioning	Adjustable
Mounting position	Any
Mode of operation	Pushing Single-acting
Position sensing	None
Max. impact velocity	0.3 m/s
Feed speed	0.2 mm/s...100 mm/s
Reset time at room temperature	0.8 s
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C...80 °C
Max. stop force	4000 N
Max. energy absorption per stroke	160 J
Max. energy absorption per hour	150000 J
Min. feed force	400 N
Max. feed force	4000 N
Max. residual energy	0.8 J
Resetting force	12.5 N
Product weight	720 g
Type of mounting	With lock nut
Note on materials	RoHS-compliant
Seals material	NBR
Housing material	Steel Galvanized
Piston rod material	Hardened High-alloy steel