

Pressure gauge PAGL-HP3-63-60-G14

Part number: 1166938

FESTO



Data sheet

Feature	Value
Display range	0 bar...60 bar 0 MPa...6 MPa 0 psi...870 psi
Conforms to standard	EN 837-1
Pressure gauge nominal size	63
Explosion prevention and protection	Observe the information on the certificate Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Structural design	Bourdon tube pressure gauge
Type of mounting	Line installation
Operating medium	Inert gas Neutral liquids
Information on operating and pilot media	No acetylene No oxygen
Operating pressure	0 MPa...6 MPa 0 bar...60 bar 0 psi...870 psi
Intermittent load factor	0.66
Measurement accuracy class	1.6
Degree of protection	IP65
Storage temperature	-40 °C...70 °C
Temperature of medium	0 °C...60 °C
Ambient temperature	0 °C...60 °C
Note on materials	RoHS-compliant
Connection position	Centered on rear side
Pneumatic connection	G1/4
Materials in contact with the media	Brass
Material of screwed plug	Brass
Housing material	Steel
Inspection window material	PS
Housing colour	Silver

Feature	Value
Product weight	80 g
Scale	Triple scale MPa (external) bar (außen) psi (internal)