

Non return valve H-3/8-B

Part number: 11690

FESTO



Data sheet

Feature	Value
Valve function	Non-return function
Pneumatic connection 1	G3/8
Pneumatic connection 2	G3/8
Type of mounting	Screw-in
Operating pressure	0.04 MPa...1.2 MPa 0.4 bar...12 bar
Ambient temperature	-10 °C...60 °C
Housing material	Wrought aluminum alloy, anodized
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Mounting position	Any
Standard nominal flow rate 1->2 (6-5)	2000 l/min
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-10 °C...60 °C
Temperature of medium	-10 °C...60 °C
Pilot medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Max. tightening torque	20 Nm
Product weight	34 g
Note on materials	RoHS-compliant
Seals material	NBR