

Solenoid valve

JMUH-5/2-D-1C-VI



Part number: 119665

FESTO

For valve manifold

This type is suitable for vacuum.

Type to be discontinued. Available until 2011.



Data sheet

Feature	Value
Valve function	5/2 monostable
Width	42 mm
Working pressure	-0.9 ... 8 bar
Design structure	Piston slide
Type of reset	mechanical spring
Nominal size	9.5 mm
Sealing principle	soft
Manual override	Pushing
Type of piloting	direct
Flow direction	non reversible
Operating medium	filtered compressed air, grade of filtration 40 µm, lubricated or unlubricated
Medium temperature	-5 ... 50 °C
Ambient temperature	-5 ... 50 °C
Mounting type	with through hole
Pneumatic connection, port 1	Connection plate size 2 as per ISO 5599-2
Pneumatic connection, port 2	Connection plate size 2 as per ISO 5599-2
Pneumatic connection, port 3	Subbase
Pneumatic connection, port 4	Connection plate size 2 as per ISO 5599-2
Pneumatic connection, port 5	Subbase