

Pneumatic muffler AMTE-M-LH-G34

Part number: 1205864

FESTO



Data sheet

| Feature | Value |
|--|--|
| Mounting position | Any |
| Pack size | 10 |
| Operating pressure | 0 MPa...1 MPa 0 bar...10 bar |
| Flow rate with respect to atmosphere | 12400 l/min |
| Explosion prevention and protection | Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX) |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:::] |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Noise level | 85 dB(A) |
| Ambient temperature | -40 °C...80 °C |
| Product weight | 80 g |
| Pneumatic connection | G3/4 |
| Cushioning insert material | Bronze |
| Material of screwed plug | Brass |
| Note on materials | RoHS-compliant |