

Pneumatic muffler AMTE-M-LH-N14

Part number: 1206990

FESTO



Data sheet

Feature	Value
Mounting position	Any
Pack size	20
Operating pressure	0 MPa...1 MPa 0 bar...10 bar
Flow rate with respect to atmosphere	3080 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Noise level	82 dB(A)
Ambient temperature	-40 °C...80 °C
Product weight	17 g
Pneumatic connection	1/4 NPT
Cushioning insert material	Bronze
Material of screwed plug	Brass
Note on materials	RoHS-compliant