

Pneumatic muffler

AMTE-M-LH-U10

Part number: 1206994

FESTO



Data sheet

| Feature | Value |
|------------------------------------------|----------------------------------------------|
| Mounting position | Any |
| Pack size | 20 |
| Operating pressure | 0 MPa...1 MPa 0 bar...10 bar |
| Flow rate with respect to atmosphere | 260 l/min |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7::-] |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Noise level | 71 dB(A) |
| Ambient temperature | -40 °C...80 °C |
| Product weight | 1.7 g |
| Pneumatic connection | 10-32 UNF-2A |
| Cushioning insert material | Bronze |
| Material of screwed plug | Brass |
| Note on materials | RoHS-compliant |