

# Pneumatic muffler AMTE-M-LH-M3

Part number: 1231120

FESTO



## Data sheet

| Feature                                  | Value  |
|--|--|
| Mounting position                        | Any  |
| Pack size                                | 20   |
| Operating pressure                       | 0 MPa...1 MPa<br>0 bar...10 bar                                    |
| Flow rate with respect to atmosphere     | 95 l/min   |
| Explosion prevention and protection      | Zone 1 (ATEX)<br>Zone 2 (ATEX)<br>Zone 21 (ATEX)<br>Zone 22 (ATEX) |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:::]                       |
| Information on operating and pilot media | Operation with oil lubrication possible                            |
| Corrosion resistance class (CRC)         | 1 - Low corrosion stress   |
| LABS (PWIS) conformity                   | VDMA24364-B1/B2-L  |
| Noise level                              | 55 dB(A)   |
| Ambient temperature                      | -40 °C...80 °C   |
| Product weight                           | 0.4 g  |
| Pneumatic connection                     | M3   |
| Cushioning insert material               | Bronze   |
| Material of screwed plug                 | Brass  |
| Note on materials                        | RoHS-compliant   |