

Bellows gripper DHEB-10-E-U-E-P

Part number: 1320832

FESTO



Data sheet

Feature	Value
Size	10
Stroke of bellows	4 mm
Min. diameter to be gripped	10.5 mm
Max. diameter to be gripped	14 mm
Mounting position	Any
Mode of operation	Single-acting Closed
Gripper function	Adaptive
Structural design	Contracting diaphragm Positively driven motion sequence
Guide	Basic guide
Position sensing	None
Operating pressure	5 bar...8 bar
Resetting pressure	1 bar
Max. operating frequency of pneumatic gripper	4 Hz
Min. opening time at 6 bar	20 ms
Min. closing time at 6 bar	40 ms
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	5 °C...60 °C
Average replacement interval for the bellows	0.5 MioCyc
Guide value for payload	0.1 kg
Product weight	17 g
Type of mounting	With external thread With lock nut Optionally:
Pneumatic connection	M3
Note on materials	RoHS-compliant
Bellows material	EPDM
Housing material	Aluminum Anodized

