


Clamping module EV-20/75-5

Part number: 13291

FESTO



Data sheet

Feature	Value
Stroke	5 mm
Clamping area	20x75
Mounting position	Any
Mode of operation	Single-acting
Operating pressure	0.2 MPa...0.6 MPa 2 bar...6 bar 29 psi...87 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-:]
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper are excluded from use. Exception are printed circuit boards, cables, electrical connectors and coils
Ambient temperature	-20 °C...40 °C
Product weight	130 g
Type of mounting	With through-hole
Pneumatic connection	M5
Housing material	Die-cast aluminum
Diaphragm material	TPE-U(PU)