

Push-in L-connector NPQP-L-Q10-E-FD-P10

Part number: 133108

FESTO



Data sheet

| Feature | Value |
|--|--|
| Size | Standard |
| Nominal width | 8.3 mm |
| Design | L-shape |
| Pack size | 10 |
| Structural design | Push-pull principle |
| Temperature-dependent operating pressure | -0.95 bar...10 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7::-] |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Corrosion resistance class (CRC) | 4 - Particularly high corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| For use in the food industry | See supplementary material information |
| Ambient temperature | -20 °C...60 °C |
| Product weight | 14 g |
| Pneumatic connection 1 | for pneumatic tubing outside diameter 10 mm |
| Pneumatic connection 2 | for pneumatic tubing outside diameter 10 mm |
| Note on materials | RoHS-compliant |
| Housing material | PP |
| Material of tube retaining claw | High-alloy stainless steel |