

# Flow control/muffler VFFK-C-K-R18-P

Part number: 133142

FESTO



## Data sheet

Feature	Value
Valve function	Sound pressure flow control function
Selection of additional function	with muffler
Pneumatic connection 1	R1/8
Adjusting element	Knurled screw
Type of mounting	Screw-in
Standard flow rate 6->0 bar	0 l/min...270 l/min
Operating pressure	0 bar...10 bar
Ambient temperature	0 °C...60 °C
Type of seal on screwed plug	Coating
Mounting position	Any
Operating pressure for entire temperature range	0 bar...10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	0 °C...60 °C
Product weight	13.5 g
Cushioning insert material	PE
Material of screwed plug	Brass, nickel-plated
Note on materials	RoHS-compliant
Material of adjusting screw	Brass, nickel-plated