

Push-in connector NPQP-D-Q10-Q8-FD

Part number: 133169

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal width	6.5 mm
Design	Straight design
Pack size	1
Structural design	Push-pull principle
Temperature-dependent operating pressure	-0.95 bar...10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
For use in the food industry	See supplementary material information
Ambient temperature	-20 °C...60 °C
Product weight	12 g
Pneumatic connection 1	for pneumatic tubing outside diameter 10 mm
Pneumatic connection 2	for pneumatic tubing outside diameter 8 mm
Note on materials	RoHS-compliant
Housing material	PP
Material of tube retaining claw	High-alloy stainless steel