

# Push-in T-connector NPQP-T-Q6-E-FD

Part number: 133173

**FESTO**



## Data sheet

| Feature                                  | Value  |
|--|--|
| Size                                     | Standard                                     |
| Nominal width                            | 4.8 mm                                       |
| Design                                   | T-shape                                      |
| Pack size                                | 1  |
| Structural design                        | Push-pull principle                          |
| Temperature-dependent operating pressure | -0.95 bar...10 bar                           |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7::-] |
| Information on operating and pilot media | Operation with oil lubrication possible      |
| Corrosion resistance class (CRC)         | 4 - Particularly high corrosion stress       |
| LABS (PWIS) conformity                   | VDMA24364 zone III                           |
| For use in the food industry             | See supplementary material information       |
| Ambient temperature                      | -20 °C...60 °C                               |
| Product weight                           | 9 g  |
| Pneumatic connection 1                   | For pneumatic tubing outside diameter 6 mm   |
| Pneumatic connection 2                   | for pneumatic tubing outside diameter 6 mm   |
| Note on materials                        | RoHS-compliant                               |
| Housing material                         | PP   |
| Material of tube retaining claw          | High-alloy stainless steel                   |