

**Clamping sleeve**  
**EAMH-50-5-C13.6-P**  
Part number: 1354092



**Data sheet**

| Feature                | Value                  |
|------------------------|------------------------|
| Size                   | 50                     |
| Mounting position      | Any                    |
| Max. rotational speed  | 6000 rpm               |
| LABS (PWIS) conformity | VDMA24364-B2-L         |
| Storage temperature    | -25 °C...60 °C         |
| Relative air humidity  | 0 - 95 %               |
| Ambient temperature    | -10 °C...60 °C         |
| Mass moment of inertia | 0.39 kgmm <sup>2</sup> |
| Product weight         | 20 g                   |
| Note on materials      | RoHS-compliant         |