

Clamping sleeve EAMH-60-6-C18.1-P

Part number: 1354095

FESTO



Data sheet

Feature	Value
Size	60
Mounting position	Any
Max. rotational speed	6000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	1.57 kgmm ²
Product weight	44 g
Note on materials	RoHS-compliant