

Clamping sleeve
EAMH-145-12-C34-P
Part number: 1354108



Data sheet

Feature	Value
Size	145
Mounting position	Any
Max. rotational speed	4000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	43.9 kgmm ²
Product weight	338 g
Note on materials	RoHS-compliant