

**Clamping sleeve**  
**EAMH-145-24-C34-P**  
Part number: 1354109



**Data sheet**

| Feature                | Value                |
|------------------------|----------------------|
| Size                   | 145                  |
| Mounting position      | Any                  |
| Max. rotational speed  | 4000 rpm             |
| LABS (PWIS) conformity | VDMA24364-B2-L       |
| Storage temperature    | -25 °C...60 °C       |
| Relative air humidity  | 0 - 95 %             |
| Ambient temperature    | -10 °C...60 °C       |
| Mass moment of inertia | 34 kgmm <sup>2</sup> |
| Product weight         | 229 g                |
| Note on materials      | RoHS-compliant       |