

# Multi-tube connector KM-22-B

Part number: 13694

FESTO



## Data sheet

Feature	Value
Nominal width	4 mm
Pack size	1
Operating pressure	-0.095 MPa...0.8 MPa -0.95 bar...8 bar -13.775 psi...116 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:::]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B2-L
Temperature of medium	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Max. connections	22
Pneumatic connection	For pneumatic tubing outside diameter 3 mm For pneumatic tubing outside diameter 4 mm For pneumatic tubing outside diameter 6 mm
Note on materials	RoHS-compliant