

Plug socket MSSD-E

Part number: 14098

FESTO



Data sheet

Feature	Value
Type of mounting	On air solenoid valve with M3 central screw
Mounting position	Any
Product weight	8 g
Electrical connection 1	Angled socket, rectangular design, 3-pin, form C
Electrical connection 2	Screw terminal
DC operating voltage range	0 V...300 V
Operating voltage range AC	0 V...250 V
Current rating at 40° C	6 A
Cable fitting	Pg7
Cable diameter	6 mm...8 mm
Connection cross section	0.75 mm ²
Degree of protection	IP65
Ambient temperature	-25 °C...90 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Contamination level	3
Housing material	PA-reinforced
Housing colour	Black
Seals material	NBR