

**Quick coupling**  
**EAMC-40-66-11-14**  
Part number: 1452798

**FESTO**



**Data sheet**

| Feature                | Value                  |
|------------------------|------------------------|
| Diameter of holder 1   | 11 mm                  |
| Diameter of holder 2   | 14 mm                  |
| Size                   | 40                     |
| Nominal length         | 66 mm                  |
| Mounting position      | Any                    |
| Max. rotational speed  | 6500 rpm               |
| LABS (PWIS) conformity | VDMA24364-B2-L         |
| Storage temperature    | -25 °C...60 °C         |
| Relative air humidity  | 0 - 95 %               |
| Ambient temperature    | -25 °C...60 °C         |
| Mass moment of inertia | 42.3 kgmm <sup>2</sup> |
| Transferable torque    | 21 Nm                  |
| Product weight         | 139 g                  |
| Note on materials      | RoHS-compliant         |