


Axial kit
EAMM-A-D32-40G
Part number: 1454238



Data sheet

Feature	Value
Nominal length	55.5 mm
Mounting position	Any
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	5.87 kgmm ²
Transferable torque	6.5 Nm
Product weight	420 g
Interface code, actuator	D32 D32C
Interface code, motor in	40G
Note on materials	RoHS-compliant