

Quick coupling
EAMC-56-58-19-19
Part number: 1485673

FESTO



Data sheet

Feature	Value
Diameter of holder 1	19 mm
Diameter of holder 2	19 mm
Size	56
Nominal length	58 mm
Mounting position	Any
Max. rotational speed	5500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	128 kgmm ²
Transferable torque	60 Nm
Product weight	285 g
Note on materials	RoHS-compliant