


Clamping module EV-20-4

Part number: 150683



Data sheet

Feature	Value
Stroke	4 mm
Clamping area	Ø 20
Mounting position	Any
Mode of operation	Single-acting
Operating pressure	0.6 MPa 6 bar 87 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...40 °C
Product weight	19 g
Type of mounting	With through-hole
Pneumatic connection	M3
Housing material	Die-cast aluminum
Diaphragm material	TPE-U(PU)