

**Profile strip**  
**SLZS-40- -**  
Part number: 150919



**Data sheet**

| Feature                          | Value                              |
|----------------------------------|------------------------------------|
| Design                           | T-slot for proximity sensor        |
| Max. profile length              | 2800 mm                            |
| Mounting position                | Any                                |
| for piston Ø                     | Ø40                                |
| Structural design                | Sensor rail                        |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress      |
| LABS (PWIS) conformity           | VDMA24364-B2-L                     |
| Ambient temperature              | -20 °C...60 °C                     |
| Type of mounting                 | With through-hole and screw        |
| Profile material                 | Wrought aluminum alloy<br>Anodized |
| Note on materials                | RoHS-compliant                     |
| Material of screws               | High-alloy steel                   |