

One-way flow control valve GRLA-1/4-NPT-B

Part number: 151547

FESTO



Data sheet

Feature	Value
Valve function	Exhaust air flow control non-return function
Pneumatic connection 1	Internal thread 1/4 NPT
Pneumatic connection 2	Male thread 1/4 NPT
Adjusting element	Slotted screw
Type of mounting	Screw-in
Standard nominal flow rate in flow control direction	610 l/min
Standard nominal flow rate in non-return direction	450 l/min...820 l/min
Ambient temperature	-10 °C...60 °C
Mounting position	Any
Operating pressure for entire temperature range	0,3 bar...10 bar
Standard flow rate in flow control direction 6 -> 0 bar	1200 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom class	Class 4 according to ISO 14644-1
Temperature of medium	-10 °C...60 °C
Nominal width	6 mm
Max. tightening torque	11 Nm
Material of screwed plug	Wrought aluminum alloy
Note on materials	RoHS-compliant
Seals material	NBR
Material of adjusting screw	Brass
Swivel joint material	Die-cast zinc