

Multi-socket
KDVF6-12
Part number: 152510

FESTO



Data sheet

Feature	Value
Nominal width	6 mm
Operating pressure	-0.95 bar...10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Max. connections	12
Pneumatic connection	PK-6
Color	Gray
Note on materials	RoHS-compliant