

Manifold subbase with 90° connections NAVW-3/8-NPT-2

Part number: 152793

FESTO



Data sheet

| Feature | Value |
|--|---|
| Width | 135 mm |
| Mounting position | Any |
| Operating pressure | 0 MPa...1.6 MPa 0 bar...16 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:2] |
| Information on operating and pilot media | Ester oil < 0.1mg/m ³ , according to ISO 8573-1:2010 [-:-:2] |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -20 °C...80 °C |
| Temperature of medium | -10 °C...60 °C |
| Ambient temperature | -10 °C...60 °C |
| Sub-base mounting type | With through-hole |
| Type of mounting | With through-hole |
| Pilot air port 12/14 | 1/8 NPT |
| Auxiliary pilot air port 12 | 1/8 NPT |
| Auxiliary pilot air port 14 | 1/8 NPT |
| Pilot air port 12 | 1/8 NPT |
| Pilot air port 14 | 1/8 NPT |
| Pneumatic connection 1 | 3/8 NPT |
| Pneumatic connection 2 | 3/8 NPT |
| Pneumatic connection 4 | 3/8 NPT |
| Material of sub-base | Die-cast aluminum |