

Manifold subbase with 90° connections NAVW-1/2-NPT-3

Part number: 152794

FESTO



Data sheet

Feature	Value
Width	190 mm
Mounting position	Any
Operating pressure	0 MPa...1.6 MPa 0 bar...16 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Ester oil < 0.1mg/m³, according to ISO 8573-1:2010 [-:-:2]
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-20 °C...80 °C
Temperature of medium	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Sub-base mounting type	With through-hole
Type of mounting	With through-hole
Pilot air port 12/14	1/8 NPT
Auxiliary pilot air port 12	1/8 NPT
Auxiliary pilot air port 14	1/8 NPT
Pilot air port 12	1/8 NPT
Pilot air port 14	1/8 NPT
Pneumatic connection 1	1/2 NPT
Pneumatic connection 2	1/2 NPT
Pneumatic connection 4	1/2 NPT
Material of sub-base	Die-cast aluminum