

**Non return valve**  
**HA-3/8-QS-10**  
Part number: 153456

**FESTO**



**Data sheet**

Feature	Value
Valve function	Non-return function
Pneumatic connection 1	R3/8
Pneumatic connection 2	QS-10
Type of mounting	Screw-in
Standard nominal flow rate	1740 l/min
Operating pressure	-1 bar...10 bar
Ambient temperature	0 °C...60 °C
Housing material	Aluminum, anodized
Housing colour	Silver
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Min. differential pressure, opening	0.1 bar
Min. differential pressure, closing	0.2 bar
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	47 g
Note on materials	RoHS-compliant