

Non return valve H-QS-8

Part number: 153464

FESTO



Data sheet

Feature	Value
Valve function	Non-return function
Pneumatic connection 1	QS-8
Pneumatic connection 2	QS-8
Type of mounting	Line installation
Standard nominal flow rate	681 l/min
Operating pressure	-1 bar...10 bar
Ambient temperature	0 °C...60 °C
Housing material	Aluminum, anodized
Housing colour	Black
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Min. differential pressure, opening	0.1 bar
Min. differential pressure, closing	0.2 bar
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	21 g
Note on materials	RoHS-compliant