


Barb tubing fitting N-3/8-P-6-MS

Part number: 15633

FESTO



Data sheet

Feature	Value
Nominal width	4.5 mm
Type of seal on screwed plug	Sealing ring
Mounting position	Any
Design	Straight design
Pack size	10
Operating pressure for entire temperature range	-0.95 bar...16 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Max. tightening torque	15 Nm
Product weight	26 g
Pneumatic connection 1	External thread G3/8
Pneumatic connection 2	For tubing I.D. 6 mm
Note on materials	RoHS-compliant
Housing material	Brass