

**Sensor tester**  
**SM-TEST-1**  
Part number: 158481



**Data sheet**

Feature	Value
CE marking (see declaration of conformity)	As per EU EMC directive
Ambient temperature	0 °C...40 °C
DC operating voltage range	12 V...20 V
Power supply	Two 9V block-type batteries
Ready status indication	LED green
Degree of protection	IP20
LABS (PWIS) conformity	VDMA24364-B2-L