

Air reservoir CRVZS-0.1

Part number: 160233

FESTO



Data sheet

Feature	Value
Volume	0.1 l
Mounting position	Any
Conforms to standard	AD 2000
Operating pressure	-0.095 MPa...1.6 MPa -0.95 bar...16 bar -13.78 psi...232 psi
Certification	CRN German Technical Control Board (TÜV)
Certificate issuing authority	TSSACRN0H17477.5C
Operating medium	Compressed air as per ISO 8573-1:2010 [-:~:] Nitrogen
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
For use in the food industry	See supplementary material information
Temperature of medium	-10 °C...100 °C
Ambient temperature	-10 °C...100 °C
Max. tightening torque for connecting thread	15 Nm
Product weight	226 g
Type of mounting	Fixing clips
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Air reservoir material	High-alloy stainless steel
Fixing clips material	High-alloy stainless steel