

Flange mounting

CRFNG-50

Part number: 161848

FESTO



Data sheet

Feature	Value
Size	50
Mounting position	Any
Conforms to standard	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 1% by mass of copper are excluded from use. Circuit boards, Lines, electrical push-in connectors and Coils Metals with more than 1% copper as an alloy component are excluded from use. Exceptions are printed circuit boards, cables, electrical connectors and coils Metals with more than 5% copper by mass are excluded from use. Circuit boards, Lines, electrical push-in connectors and Coils Metals with more than 5% copper as an alloy component are excluded from use. Exceptions are printed circuit boards, cables, electrical connectors and coils Metals with more than 5% copper, zinc or nickel by mass are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, circuit boards, cables, electrical plug connectors and coils
Ambient temperature	-40 °C...150 °C
Product weight	526 g
Mounting material	High-alloy stainless steel
Material of screws	High-alloy stainless steel