

**Clevis foot**  
**CRLBN-20/25**  
Part number: 161863

**FESTO**



**Data sheet**

Feature	Value
Size	20/25
Mounting position	Any
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Product corresponds to Festo's internal product definition for use in battery production:Metals with more than 1% by mass of copper, zinc or nickel are excluded from use.The exceptions are nickel in steel, chemically nickel-plated surfaces, circuit boards, cables, electrical plug connectors and coils
Ambient temperature	-40 °C...150 °C
Product weight	82 g
Note on materials	RoHS-compliant
Mounting material	High-alloy stainless steel
Bolt material	High-alloy stainless steel
Fuse material	High-alloy stainless steel