

Foot mounting CRH-50

Part number: 162953

FESTO



Data sheet

Feature	Value
Size	50
Mounting position	Any
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Product corresponds to Festo's internal product definition for use in battery production: Metals with more than 1% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, circuit boards, cables, electrical plug connectors and coils
Product weight	916 g
Note on materials	RoHS-compliant
Mounting material	High-alloy stainless steel
Nut material	High-alloy steel