

Connection block CPE18-PRSG-2

Part number: 164970

FESTO



Data sheet

Feature	Value
Max. no. of valve positions	2
Burst pressure	3 MPa 30 bar 435 psi
Operating pressure	-0.09 MPa...1 MPa
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	170 g
Sub-base mounting type	With through-hole With H-rail
Pneumatic connection 1	G1/2
Note on materials	RoHS-compliant
Housing material	PA-reinforced