

Fiber-optic cable
SOEZ-LLG-SE-0,5-M4
Part number: 165357



Data sheet

Feature	Value
Method of measurement	Through-beam sensor Fiber-optic cable
Ambient temperature	-20 °C...160 °C
Size	M4
Product weight	46 g
Housing material	Brass Chrome-plated
Setting range, upper limit	280 mm
Ambient temperature of flexible installation	-20 °C...120 °C
Degree of protection	IP54
LABS (PWIS) conformity	VDMA24364-B2-L