

Plug socket MSSD-C-4P

Part number: 171157

FESTO



Data sheet

Feature	Value
Type of mounting	On air solenoid valve with M3 central screw
Mounting position	Any
Product weight	22 g
Electrical connection	3-pin Socket, angled Form A as per DIN EN 175301-803 Rectangular design MSC Rectangular design MSN1
Cable fitting	Pg9
Cable diameter	6 mm...8 mm
Nominal conductor cross section	1.5 mm ²
Degree of protection	IP65
Ambient temperature	-25 °C...90 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Housing material	Polymer
Housing colour	Black