


Compressed air filter LF-3/8-D-MIDI-NPT

Part number: 173688

FESTO



Data sheet

| Feature | Value |
|----------------------------------|--|
| Size | Midi |
| Series | D |
| Mounting position | Vertical |
| Grade of filtration | 40 µm |
| Condensate drain | Manual, non-detenting |
| Bowl guard | Metal bowl guard |
| Operating pressure | 0 bar...16 bar |
| Standard nominal flow rate | 2700 l/min |
| Operating medium | Compressed air as per ISO 8573-1:2010 [:-9:-] Inert gas |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Storage temperature | -10 °C...60 °C |
| Air quality class at the output | Compressed air as per ISO 8573-1:2010 [7:8:4] Inert gas |
| Temperature of medium | -10 °C...60 °C |
| Ambient temperature | -10 °C...60 °C |
| Type of mounting | Line installation With mounting bracket Optionally: |
| Pneumatic connection 1 | 3/8 NPT |
| Pneumatic connection 2 | 3/8 NPT |
| Note on materials | RoHS-compliant |
| Compressed air filter material | PE |
| Housing material | Die-cast zinc |
| Material of bowl | PC |