


Compressed air filter

LF-1/2-D-5M-MIDI-A-NPT

Part number: 173695

FESTO



Data sheet

Feature	Value
Size	Midi
Series	D
Mounting position	Vertical
Grade of filtration	5 µm
Condensate drain	Fully automatic
Bowl guard	Metal bowl guard
Operating pressure	2 bar...12 bar
Standard nominal flow rate	2000 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:9:-] Inert gas
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [6:8:4] Inert gas
Temperature of medium	5 °C...60 °C
Ambient temperature	5 °C...60 °C
Type of mounting	Line installation With mounting bracket Optionally:
Pneumatic connection 1	1/2 NPT
Pneumatic connection 2	1/2 NPT
Note on materials	RoHS-compliant
Compressed air filter material	PE
Housing material	Die-cast zinc
Material of bowl	PC