


# Fine filter combination LFMBA-3/8-D-MIDI-NPT

Part number: 173746



## Data sheet

Feature	Value
Size	Midi
Series	D
Mounting position	Vertical
Grade of filtration	0.01 µm
Filter efficiency	99.9999 %
Condensate drain	Manual, non-detenting
Bowl guard	Metal bowl guard
Operating pressure	1 bar...16 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [6:8:4] Inert gas
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [1:7:2] Inert gas
Temperature of medium	1.5 °C...60 °C
Residual oil content	0.01 mg/m³
Ambient temperature	-10 °C...60 °C
Type of mounting	Line installation With accessories
Pneumatic connection 1	3/8 NPT
Pneumatic connection 2	3/8 NPT
Note on materials	RoHS-compliant
Compressed air filter material	Borosilicate fiber
Housing material	Die-cast zinc
Material of bowl	PC