


Filter regulator LFR-3/4-D-MAXI-NPT

Part number: 173804

FESTO



Data sheet

Feature	Value
Size	Maxi
Series	D
Mounting position	Vertical
Grade of filtration	40 µm
Condensate drain	Manually rotating
Max. condensate volume	80 cm ³
Bowl guard	Metal bowl guard
Operating pressure	0.1 MPa...1.6 MPa 1 bar...16 bar
Max. pressure hysteresis	0.4 bar
Standard nominal flow rate	9700 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [::9:-] Inert gas
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [7:8:4] Inert gas
Temperature of medium	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	1370 g
Type of mounting	With accessories
Pneumatic connection 1	3/4 NPT
Pneumatic connection 2	3/4 NPT
Note on materials	RoHS-compliant
Housing material	Die-cast zinc
Material of bowl	PC