


# Filter regulator LFR-3/4-D-7-MAXI-NPT

Part number: 173810

**FESTO**



## Data sheet

| Feature                          | Value  |
|----------------------------------|--|
| Size                             | Maxi   |
| Series                           | D  |
| Mounting position                | Vertical   |
| Grade of filtration              | 40 µm  |
| Condensate drain                 | Manually rotating  |
| Max. condensate volume           | 80 cm <sup>3</sup>   |
| Bowl guard                       | Metal bowl guard   |
| Operating pressure               | 0.1 MPa...1.6 MPa<br>1 bar...16 bar                        |
| Max. pressure hysteresis         | 0.4 bar  |
| Standard nominal flow rate       | 10000 l/min  |
| Operating medium                 | Compressed air as per ISO 8573-1:2010 [::9:-]<br>Inert gas |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress                              |
| LABS (PWIS) conformity           | VDMA24364-B1/B2-L  |
| Storage temperature              | -10 °C...60 °C   |
| Air quality class at the output  | Compressed air as per ISO 8573-1:2010 [7:8:4]<br>Inert gas |
| Temperature of medium            | -10 °C...60 °C   |
| Ambient temperature              | -10 °C...60 °C   |
| Product weight                   | 1370 g   |
| Type of mounting                 | Line installation<br>With mounting bracket<br>Optionally:  |
| Pneumatic connection 1           | 3/4 NPT  |
| Pneumatic connection 2           | 3/4 NPT  |
| Note on materials                | RoHS-compliant   |
| Housing material                 | Die-cast zinc  |
| Material of bowl                 | PC   |