


Air line lubricator
LOE-1/8-D-MINI-NPT
Part number: 173820

FESTO



Data sheet

| Feature | Value |
|---|--|
| Max. oil capacity | 45 cm ³ |
| Bowl guard | Metal bowl guard |
| Operating pressure | 1.6 MPa 16 bar 232 psi |
| Minimum flow rate for lubricator function | 3 l/min |
| Standard nominal flow rate | 1300 l/min |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas |
| Information on operating and pilot media | Operation with oil lubrication not possible |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Storage temperature | -10 °C...60 °C |
| Air quality class at the output | Compressed air as per ISO 8573-1:2010 [7:4:-] Inert gas |
| Temperature of medium | -10 °C...60 °C |
| Ambient temperature | -10 °C...60 °C |
| Product weight | 270 g |
| Type of mounting | With accessories |
| Pneumatic connection 1 | 1/8 NPT |
| Pneumatic connection 2 | 1/8 NPT |
| Note on materials | RoHS-compliant |
| Material of bowl | PC |