


Air line lubricator
LOE-1/4-D-MINI-NPT
Part number: 173821

FESTO



Data sheet

Feature	Value
Max. oil capacity	45 cm ³
Bowl guard	Metal bowl guard
Operating pressure	1.6 MPa 16 bar 232 psi
Minimum flow rate for lubricator function	3 l/min
Standard nominal flow rate	2300 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas
Information on operating and pilot media	Operation with oil lubrication not possible
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [7:4:-] Inert gas
Temperature of medium	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	270 g
Type of mounting	With accessories
Pneumatic connection 1	1/4 NPT
Pneumatic connection 2	1/4 NPT
Note on materials	RoHS-compliant
Material of bowl	PC